

# Inductherm:

## Porcelain insert for Hold-Line concept and Install Hold-Line



Lid retainer for easy self-service



Condensation collects in the drip tray

for round chafers

Accessories	W x D x H	Capacity	Lid	Lid dimensions
Round chafing dish with porcelain insert	ø 300 x 230/600 mm* *highest point with lid fully open			
Porcelain insert	ø 300 x 60 mm	2.0 l		
Inductherm GN-insert 1/1	530 x 325 x 65 mm	8.0 l	GN-lid 1/1	530 x 325 mm
Inductherm GN-insert 2/4	530 x 162 x 65 mm	4.0 l	GN-lid 2/4	530 x 162 mm
Inductherm GN-insert 1/3	325 x 175 x 65 mm	2.5 l	GN-lid 1/3	325 x 175 mm



GN porcelain inserts available in 3 sizes

The energy transmitted using the Inductherm-coated porcelain inserts ensures that the Ceran surface serves exclusively as a base and remains cold (tepid from the heat of the insert).



Your dealer give you more information.